

MoFlo™XDP High-speed Cell Sorter

MoFlo™XDP configuration table

Detector	Filter (nm)	Excitation lasers		
		488nm	642nm	405/355nm
FSC	—			
SSC	488/10 BP			
FL1	529/28 BP			
FL2	575/25 BP			
FL3	613/20 BP			
FL4	670/30 BP			
FL5	785/62 BP	IR		
FL6	457/50 BP			
FL7	530/40 BP			
FL10	670/30 BP			
FL11	720/13 BP			
FL12	785/62 BP		IR	