

BD LSRFortessa™ 5 SORP configuration table

Detector	Mirror	Filter	Excitation lasers				
			355nm	405nm	488nm	561nm	640nm
FSC	—	—					
SSC	—	488/10 BP					
355-C	—	379/28 or 450/40					
355-B	640 LP	670/30					
355-A	690 LP	740/35					
405-F	—	450/50 BP					
405-E	495 LP	525/50 BP					
405-D	595 LP	610/20 BP					
405-C	635 LP	660/20 BP					
405-B	685 LP	710/50 BP					
405-A	750 LP	780/60 BP		IR			
488-B	505 LP	530/30 BP					
488-A	670 LP	695/40 BP					
561-D	—	586/15 BP					
561-C	595 LP	610/20 BP					
561-B	685 LP	710/50 BP					
561-A	750 LP	780/60 BP				IR	
640-C	—	670/30 BP					
640-B	685 LP	730/45 BP					
640-A	740 LP	780/60 BP					IR